

STAPLER - HELLER

1. GENERAL

1.001 This addendum identifies and describes the operation and maintenance of the WT-1 Heller staple driver.

2. OPERATION

The following changes apply to Part 2 of the section:

- (a) 2.01 - revised
- (b) 2.02 - added sentences

2.01 The TM stapler, illustrated in figure 1, and the WT-1 stapler are similar in design. Both contain a spring-driven hammer which is actuated by depressing the operating handle. After each operation a staple is automatically fed into driving position by the pusher assembly.

2.02 (Add after the last sentence). Use only WT-1 staples in the WT-1 stapler. WT-1 staples are available in plain or coppered finish and are for indoor and outdoor use respectively.