


NONCODED TOOLS
 SCREWDRIVERS AND SCREW-STARTERS


SCREWDRIVER, AECO H-21766



Offset double-end screwdriver

For use on 197- and 198-type switches and step-by-step type relays.

→ SCREWDRIVER, B
 (In ordering, specify size desired.)



Size	Dimensions			Intended for Screw No.
	A	B	C	
1	3"	7"	3/16"	4 and smaller
2	4"	8"	1/4"	5 to 9
3	6"	11"	5/16"	10 to 16


The B Screwdriver may be furnished with a 4- or 6-fluted plastic handle.

Replaces the Phillips-type Screwdriver.

For general use when Phillips screws or bolts are employed.

(Spec. AT-7739)

→ SCREWDRIVER, C
 (In ordering, specify size desired.)



Size	Dimensions				Intended for Screw No.
	A	B	C	D	
3"	6-7/8"	3/16"	3/16"	0.025"	4 to 6
6"	9-7/8"	3/16"	3/16"	0.028"	5 to 8

The C Screwdriver may be furnished with a 4- or 6-fluted plastic handle.

Replaces the Cabinet Screwdriver and the 6" AECO H-24664 Cabinet Screwdriver.

For general use.

(Spec. AT-7825)

→ SCREWDRIVER, CABINET, AECO H-24664

Replaced by C Screwdriver.

→ SCREWDRIVER, CABINET

Replaced by C Screwdriver.


SCREWDRIVER, CORD-REPAIR, KS-2348

For ordering information -
 See Tool, Cord-Repair, KS-2348

SCREWDRIVER, D-158524 Manufacture
 Discontinued.

Replaced by the No. 670A tool

→ SCREWDRIVER, D




The D Screwdriver may be furnished with a 4- or 6-fluted plastic handle, and is intended for No. 5 to 10 screws.

Replaces the H Cabinet Screwdriver.

For general use.


(Spec. AT-7825)

SCREWDRIVER, DOUBLE GRIP



Replaces "T" handle screwdriver R-58442
 For use on elevator apparatus and clutches.
 (Spec. AT-6860)

→ SCREWDRIVER, E
 (In ordering, specify size desired.)



Size	Dimensions				Intended for Screw No.
	A	B	C	D	
4	8-5/16"	1/4"	1/4"	0.031"	6 to 12
5	10-1/2"	3/8"	7/16"	0.043"	14 to 18


The E Screwdriver may be furnished with a 4- or 6-fluted plastic handle.

Replaces the Regular Screwdriver.
 For general use.
 (Spec. AT-7825)

→ SCREWDRIVER, H CABINET

Replaced by D Screwdriver.

SCREWDRIVER, JEWELERS (In ordering specify the number of the screwdriver and, when given, the name of the manufacturer).




Number	Blade Width	Blade Length
R-1005	.080"	3/4"
L.S. Starrett Co. No. 555E	.100"	3/4"

The R-1005 screwdriver replaces the No. 3 William Dixon Watchmakers Screwdriver, and is for general use.


L.S. Starrett Co. No. 555E screwdriver is for use on KS-12055 List 4 recorder-reproducers.

SCREWDRIVER, KS-2631



For general use.


→ SCREWDRIVER, KS-6854



Replaces the No. 35 tool.

For general use.

SCREWDRIVER, KS-14336



For use on the KS-13834 perforator.


SCREWDRIVER, OFFSET, R-72833

Replaced by: No. 563A and 564A tools.

→ SCREWDRIVER, PHILLIPS-TYPE

Replaced by the B Screwdriver.


SCREWDRIVER, KEDMAN CO., QUICK WEDGE,
NO. 1736 (OR EQUIVALENT)



Blade width $\frac{3}{16}$ " and blade thickness $\frac{1}{32}$ "


For use in removing U-type relay mounting screws (after loosening) and starting mounting screws equipped with grommets.

SCREWDRIVER, R-1324




For use on the 659-type tools.

SCREWDRIVER, R-1626



For use on operators' and service assistants' bentwood type chairs.


→ SCREWDRIVER, R-2739



90° offset screwdriver

For use on L-, N-, and S-type relays.

SCREWDRIVER, R-8210




For use on 51-type dial testers, Palmer master switches and emergency lighting relays.

→ SCREWDRIVER, REGULAR

Replaced by the E Screwdriver.

SCREWDRIVER, RICHMONT INC., ROTO-TORQ.
MODEL PM-5




Screwdriver bit must be ordered separately for use with this tool. Refer to Section A707.019 for screwdriver bit used with this tool.

For use in tightening U-type relay mounting screws equipped with grommets.


SECTION A707.132

SCREWDRIVER, SLOTTED, R-6770




For use on panel multiple banks.

SCREWDRIVER, STANLEY TOOLS, 1017



For use on the KS-13834 perforator.

SCREWDRIVER, STANLEY TOOLS, 2012




For general use.

SCREWDRIVER, "T" HANDLE, R-58442

Replaced by: Screwdriver, Double Grip.


SCREWDRIVER, WATCHMAKERS, WILLIAM DIXON INC.
NO. 5



The No. 3 Watchmakers Screwdriver has been replaced by the R-1005 Screwdriver.

For general use.

SCREW-STARTER, RINCK-McILWAINE, INC., (In ordering, specify No. of screw-starter desired)



The No. 606 screw-starter is 6" long.
The No. 612 screw-starter is 12" long.

For general use.